

2.4/5 GHZ 4.5/5 DBI OUTDOOR OMNI ANTENNA WITH N-STYLE CONNECTOR ATS-OO-245-57-1NP-IC-W



ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-5 GHz / 5.1-5.9 GHz

Gain: 5 / 7 dBi Polarization: Vertical Horizontal Beamwidth: 360° Vertical Beamwidth: 30° / 20° VSWR: ≤2

Max Input Power: 20 W



MECHANICAL SPECIFICATIONS

Dimensions: 10.7" L x 0.94" DIA (273mm L x 23.8mm DIA)

Weight: 0.22 lb (0.1 kg)

Ingress Protection: Outdoor IP65

Radome Material: ABS Connector: N-Style



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor/Outdoor

Operating Temperature: -40 to 140° F (-40 to 60 °C) Storage Temperature: -67 to 185° F (-55 to 85 °C)

IP Rating: IP 66

WARRANTY

2 Year Limited Warranty



HORIZONTAL

VERTICAL



