

# 2.4/5/6 GHZ 4/6/6 DBI 10 ELEMENT OMNI ANTENNA ATS-00-2456-466-10MPC-36



### **ELECTRICAL SPECIFICATIONS**

Frequency Range: 2.4-2.48/5.15-5.85/6-7.125 GHz

Gain: 4/6/6 dBi Polarization: Vertical

Horizontal Beamwidth: 360°/360°/360° Vertical Beamwidth: 105°/105°/105°

VSWR: <2.0





# **MECHANICAL SPECIFICATIONS**

Dimensions: 6.5"x 6.3"(165mm D x 160mm H)

Weight: 1.5 lb (0.68 kg)

Installation: Flush Mount to Wall or Articulating Arm Mount

(included)

Radome Material: ABS Connector: 10 MPC Number of Leads: 10 Cable Length: 36" (910mm)

Cable Type: RG316



## **ENVIRONMENTAL SPECIFICATIONS**

Installation Environment: Due to LPI requirements, indoor only IP Rating: IP66

**WARRANTY** 

2 Year Limited Warranty



#### **HORIZONTAL**

#### **VERTICAL**

