

LTE 2 ELEMENT INDOOR/OUTDOOR OMNI ANTENNA WITH SMA



The AccelTex Solutions LTE antenna is a perfect compliment to any LTE radio. This small form factor antenna comes with an integrated threaded bolt mount and is suitable for a broad range of outdoor applications.

Part Number: ATS-00-LTE-2-2SP-18

4

ELECTRICAL SPECIFICATIONS

LTE Antenna (Main) Frequency Range: 698-960/1710-2690 MHz Gain: 2.5 dBi Polarization: Linear

LTE Antenna (AUX) Frequency Range: 698-960/1710-2690 MHz Gain: 2 dBi Polarization: Linear



MECHANICAL SPECIFICATIONS

Dimensions: 3.2" Dia x 0.57" H (81.3mm Dia x 14.6mm H) Weight: 0.55 lb (0.25 kg) Installation: Threaded Bolt with Nut Cable Type: RG174



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Outdoor Operating Temperature: -40 to 185°F (-40 to 85°C) IP Rating: IP66 VSWR: ≤3.0 Impedance: 50 Ω

VSWR: ≤3.0 Impedance: 50 Ω

Radome Material: ABS Connector: SMA Number of Leads: 2 Cable Length: 18" (457 mm)

WARRANTY

2 Year Limited Warranty

The facts and figures herein are carefully compiled to the best of our knowledge and are intended for general informational purposes only. Responsibility for the use and application of AccelTex Solutions materials rests with the end user. All AccelTex Solutions products are sold pursuant to the AccelTex Solutions Terms and Conditions of Sale. © 2019 AccelTex Solutions. All Rights Reserved. AccelTex, AccelTex Solutions, the AccelTex Solutions Logo and other marks are trademarks or registered trademarks of AccelTex Solutions. Other products or service names may be the property of third parties.

1.888.406.8906 SALES@ACCELTEX.COM