

2.4/5 GHZ 6 DBI 6 ELEMENT INDOOR/OUTDOOR PATCH ANTENNA WITH N-STYLE ATS-OP-245-7-6NP-36



ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-2.485/5.15-5.85 GHz

Gain: 7/6 dBi

Polarization: 3 Vertical, 3 Horizontal Horizontal Beamwidth: 100°/110° Vertical Beamwidth: 59°/61°





MECHANICAL SPECIFICATIONS

Dimensions: 12.6" x 6.7"x 1.38" (320x170x35mm)

Weight: 1.5 lb (0.68 kg)

Installation: Flush Mount to Wall OR use included Articulating Mount (included)

Radome Material: ABS Connector: N-Style Plug Number of Leads: 6 Cable Length: 36" (910mm)

Cable Type: ATS-200



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor/Outdoor

Operating Temperature: -40 to 158°F (-40 to 70°C)

Wind Velocity: 134 mph (216 km/h)

IP Rating: IP66


WARRANTY


2 Year Limited Warranty



HORIZONTAL PLANE

VERTICAL PLANE







2.4/5 GHZ 6 DBI 6 ELEMENT INDOOR/OUTDOOR PATCH ANTENNA WITH N-STYLE ATS-OP-245-7-6NP-36

Articulating Mount (included with antenna):

