

2.4/5 GHZ 6 DBI 6 ELEMENT INDOOR/OUTDOOR PATCH ANTENNA WITH RPTNC ATS-OP-245-7-6RPTP-36

4

ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-2.485/5.15-5.85 GHz Gain: 7/6 dBi Polarization: 3 Vertical, 3 Horizontal Horizontal Beamwidth: 100°/110° Vertical Beamwidth: 59°/61°





MECHANICAL SPECIFICATIONS

Dimensions: 12.6" x 6.7"x 1.38" (320x170x35mm) Weight: 1.5 lb (0.68 kg) Installation: Flush Mount to Wall OR use included Articulating Mount (included)



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor/Outdoor Operating Temperature: -40 to 158°F (-40 to 70°C) Wind Velocity: 134 mph (216 km/h) IP Rating: IP66 Radome Material: ABS Connector: RPTNC Number of Leads: 6 Cable Length: 36" (910mm) Cable Type: ATS-200


WARRANTY

2 Year Limited Warranty

3

HORIZONTAL PLANE

VERTICAL PLANE




The facts and figures herein are carefully compiled to the best of our knowledge and are intended for general informational purposes only. Responsibility for the use and application of AccelTex Solutions materials rests with the end user. ©2023 AccelTex Solutions. All Rights Reserved.

1.888.406.8906 SALES@ACCELTEX.COM



2.4/5 GHZ 6 DBI 6 ELEMENT INDOOR/OUTDOOR PATCH ANTENNA WITH RPSMA ATS-OP-245-7-6RPSP-36

Articulating Mount (included with antenna):



The facts and figures herein are carefully compiled to the best of our knowledge and are intended for general informational purposes only. Responsibility for the use and application of AccelTex Solutions materials rests with the end user. ©2023 AccelTex Solutions. All Rights Reserved.

1.888.406.8906 SALES@ACCELTEX.COM