

## 2.4/5 GHZ 6 DBI 5 ELEMENT INDOOR/OUTDOOR PATCH ANTENNA WITH RPSMA ATS-OP-245-7D-5RPSP-36



#### **ELECTRICAL SPECIFICATIONS**

Frequency Range: 2.4-2.485/5.15-5.85 GHz

Gain: 7 dBi

Horizontal Beamwidth: 66°/65° Vertical Beamwidth: 66°/62° VSWR: ≤1.5:1, max 2.0 Isolation: >30 dB Impedance: 50 Ω



### **MECHANICAL SPECIFICATIONS**

Dimensions: 11.12" x 4.82"x 1.08" (282.5x122.5x27.5mm)

Weight: 1.5 lb (0.68 kg)

Installation: Flush Mount to Wall OR included Articulating Mount (included)



Radome Material: ABS Connector: RPSMA Number of Leads: 5

Cable Length: 36" (910mm) Cable Type: RG402 Plenum



### **ENVIRONMENTAL SPECIFICATIONS**

Installation Environment: Indoor/Outdoor

Operating Temperature: -40 to 158°F (-40 to 70°C)

Wind Velocity: 134 mph (216 km/h)

IP Rating: IP66

#### WARRANTY

2 Year Limited Warranty



#### 2.4 GHZ

# 5 GHZ



