

2.4/5 GHZ 8 DBI 6 ELEMENT INDOOR/OUTDOOR PATCH ANTENNA WITH RPSMA ATS-OP-245-8-6RPSP-36

## **ELECTRICAL SPECIFICATIONS**

Frequency Range: 2.4-2.5 / 5.1-5.85 GHz Gain: 8 dBi Polarization: 3 Vertical, 3 Horizontal Horizontal Beamwidth: 100° / 100° Vertical Beamwidth: 40° / 25° VSWR: <1.5 Impedance: 50 Ω

## **MECHANICAL SPECIFICATIONS**

Dimensions: 12.6"x 10.3"x 1.4" (320mm x 260mm x 35mm) Radome Material: ABS Mounting: Flush Mount to Wall or Articulating Mount (included)



2.4 GHZ

## **ENVIRONMENTAL SPECIFICATIONS**

Installation Environment: Indoor/Outdoor IP Rating: IP66




Cable Length: 36" (910mm) Cable Type: ATS-195 Connector: RPSMA Plug Number of Leads: 6

## WARRANTY

2 Year Limited Warranty

5 GHZ



The facts and figures herein are carefully compiled to the best of our knowledge and are intended for general informational purposes only. Responsibility for the use and application of AccelTex Solutions materials rests with the end user. ©2023 AccelTex Solutions. All Rights Reserved.