

2.4/5 GHZ 8 DBI 6 ELEMENT INDOOR/OUTDOOR PATCH ANTENNA WITH RPSMA ATS-OP-245-8-6RPTP-36



ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-2.5 / 5.1-5.85 GHz

Gain: 8 dBi

Polarizarion: 3 Vertical, 3 Horizontal Horizontal Beamwidth: 100° / 100° Vertical Beamwidth: 40° / 25°

VSWR: <1.5 Impedance: 50 Ω



Dimensions: 12.6"x 10.3"x 1.4"(320mm x 260mm x 35mm)

Radome Material: ABS

Mounting: Flush Mount to Wall or Articulating Mount (included)

Cable Length: 36" (910mm)
Cable Type: ATS-195
Connector: RPTNC Plug
Number of Leads: 6



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor/Outdoor

IP Rating: IP66

WARRANTY

2 Year Limited Warranty



2.5 GHZ

5 GHZ

