

2.4/5/6 GHZ 13 DBI 8 ELEMENT INDOOR/OUTDOOR PATCH ANTENNA WITH RPSMA ATS-OP-2456-13-8RPSP-36



ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-2.48/5.15-5.85/6-7.125 GHz

Gain: 9/11/11 dBi Polarization: Vertical

Horizontal Beamwidth: 30°/15°/12° Vertical Beamwidth: 120°/110°/110°

VSWR: <2.5





MECHANICAL SPECIFICATIONS

Dimensions: 19.3"x 19.3"x 2.44"(490x490x62mm)

Weight: 2.2 lb (4 kg)

Installation: Flush Mount to Wall or articulating mount (included)

Radome Material: ASA Connector: RPSMA Number of Leads: 8

Cable Length: 36" (910mm) Cable Type: ATS-200



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor/Outdoor

IP Rating: IP66

WARRANTY

2 Year Limited Warranty



HORIZONTAL

VERTICAL

