



### ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-2.48/5.15-5.85/6-7.125 GHz  
 Gain: 4/7/7 dBi  
 Polarization: 5 Vertical / 5 Horizontal  
 Horizontal Beamwidth: 76°/50°/46°  
 Vertical Beamwidth: 72°/50°/44°  
 VSWR: <2.0



### MECHANICAL SPECIFICATIONS

Dimensions: 11.8" x 11.8" x 1.85" (300x300x47mm)  
 Weight: 1.5 lb (0.68 kg)  
 Installation: Flush Mount to Wall or  
 Articulating wall/pole mount (included)

Radome Material: ABS  
 Connector: 4MPC & 6MPC  
 Number of Leads: 10  
 Cable Length: 36" (910mm)  
 Cable Type: RG316



### ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Due to LPI requirements, Indoor only  
 IP Rating: IP66

### WARRANTY

2 Year Limited Warranty



### HORIZONTAL

### VERTICAL



