

2.4/5/6 GHZ 4/7/7 DBI 4 ELEMENT INDOOR/ OUTDOOR PATCH ANTENNA WITH N-STYLE ATS-OP-2456-477-4NP-36



ELECTRICAL SPECIFICATIONS

AccelTex

Frequency Range: 2.4-2.48/5.15-5.85/6-7.125 GHz Gain: 4/7/7 dBi Polarization: 2 Vertical / 2 Horizontal Horizontal Beamwidth: 80°/60°/50° Vertical Beamwidth: 70°/70°/70° VSWR: ≤1.5:1 Max 2.0 Isolation: >30 dB Impedance: 50 Ω



MECHANICAL SPECIFICATIONS

Dimensions: 7"x 8.2"x 1.72" (178x208x43mm) Weight: 2.5 lb (1.13 kg) Installation: Mount to Wall or Articulating Wall/Pole Mount (included) Radome Material: ABS Connector: N-Style Plug Number of Leads: 4 Cable Length: 36" (914.4mm) Cable Type: ATS-195



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor/Outdoor IP Rating: IP67




2 Year Limited Warranty

HOR

HORIZONTAL





The facts and figures herein are carefully compiled to the best of our knowledge and are intended for general informational purposes only. Responsibility for the use and application of AccelTex Solutions materials rests with the end user. ©2024 AccelTex Solutions. All Rights Reserved.

1.888.406.8906 SALES@ACCELTEX.COM



2.4/5/6 GHZ 4/7/7 DBI 4 ELEMENT INDOOR/ OUTDOOR PATCH ANTENNA WITH N-STYLE ATS-OP-2456-477-4NP-36

