

2.4/5/6 GHZ 4/7/7 DBI 4 ELEMENT INDOOR/ OUTDOOR PATCH ANTENNA WITH RPSMA ATS-OP-2456-477-4RPSP-36



ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-2.48/5.15-5.85/6-7.125 GHz

Gain: 4/7/7 dBi

Polarization: 2 Vertical / 2 Horizontal Horizontal Beamwidth: 80°/60°/50° Vertical Beamwidth: 70°/70°/70° VSWR: ≤1.5:1 Max 2.0 Isolation: >30 dB Impedance: 50 Ω



MECHANICAL SPECIFICATIONS

Dimensions: 7"x 8.2"x 1.72"

(178x208x43mm) Weight: 2.5 lb (1.13 kg)

Installation: Flush Mount to Wall or Articulating Wall/Pole Mount (included)

Radome Material: ABS Connector: RPSMA Plug Number of Leads: 4

Cable Length: 36" (914.4mm) Cable Type: ATS-195



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor/Outdoor

IP Rating: IP67


WARRANTY

2 Year Limited Warranty



HORIZONTAL

VERTICAL





2.4/5/6 GHZ 4/7/7 DBI 4 ELEMENT INDOOR/ OUTDOOR PATCH ANTENNA WITH RPSMA ATS-OP-2456-477-4RPSP-36

