



ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-2.48/5.15-5.85/6-7.125 GHz
 Gain: 4/5/5 dBi
 Polarization: 5 Vertical / 5 Horizontal
 Horizontal Beamwidth: 85°/90°/90°
 Vertical Beamwidth: 85°/90°/90°



MECHANICAL SPECIFICATIONS

Dimensions: 11.81" x 11.81" x 1.85" (300x300x47mm)
 Connector: 4MPC & 6MPC

Radome Material: ABS
 Cable Type: ATS-100



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Due to LPI requirements, Indoor only
 IP Rating: IP66

WARRANTY

2 Year Limited Warranty



HORIZONTAL

VERTICAL



