

## 2.4/5/6 GHZ 8 DBI 10 ELEMENT **PATCH ANTENNA** ATS-OP-2456-8-10MPC-36



## **ELECTRICAL SPECIFICATIONS**

Frequency Range: 2.4-2.48/5.15-5.85/6-7.125 GHz

Gain: 8 /8 / 8 dBi

Polarization: 5 Vertical / 5 Horizontal Horizontal Beamwidth: 115°/110°/110° Vertical Beamwidth: 50°/25°/25°

VSWR: <2.5





### **MECHANICAL SPECIFICATIONS**

Dimensions: 15.4"x 15.4"x 2.24"(390x390x57mm)

Weight: 1.5 lb (0.68 kg)

Installation: Flush Mount to Wall or

Articulating wall/pole mount (included)

Radome Material: ABS Connector: 4MPC & 6MPC Number of Leads: 10 Cable Length: 36" (910mm) Cable Type: RG316



## **ENVIRONMENTAL SPECIFICATIONS**

Installation Environment: Due to LPI requirements, Indoor only

IP Rating: IP66


## WARRANTY

2 Year Limited Warranty



## **HORIZONTAL**

### **VERTICAL**





# 2.4/5/6 GHZ 8 DBI 10 ELEMENT PATCH ANTENNA ATS-OP-2456-8-10MPC-36

