



## **ELECTRICAL SPECIFICATIONS**

Accelte

Frequency Range: 698-960 / 1710-2700 MHz Gain: 11 dBi Polarization: Vertical Horizontal Beamwidth: 50°- 65° Vertical Beamwidth: 40° - 50°

\$

## **MECHANICAL SPECIFICATIONS**

Dimensions: 17.4"x 2.55"x 8.29" (442x65x210.6mm) Weight: 2.2 lb (1 kg) Installation: Pole Mounting Mast Diameter: Ø1.57"-2" (40-50mm) VSWR: <2.0 (698-806MHz) / <1.5 (806-960MHz) (1710-2700MHz) Front to Back Ratio: >15 dB Impedance: 50  $\Omega$ Lightning Protection: DC Ground Max Input Power: 50 W

Radome Material: ABS Connector: N-Style Plug

2 Year Limited Warranty






**700 MHZ** 

## **ENVIRONMENTAL SPECIFICATIONS**

Installation Environment: Indoor/Outdoor Operating Temperature: -40 to 158°F (-40 to 70°C) Wind Velocity Rating: 60 m/s IP Rating: IP66

## 1700MHZ

WARRANTY



The facts and figures herein are carefully compiled to the best of our knowledge and are intended for general informational purposes only. Responsibility for the use and application of AccelTex Solutions materials rests with the end user. ©2024 AccelTex Solutions. All Rights Reserved.

1.888.406.8906 SALES@ACCELTEX.COM