



Class II Division 1, 25W Horn Speaker for Dust Environments (16 ohm)

By Austdac
Catalog # 13310-411



The 13310 integral re-entrant horn loudspeakers are UL and cUL approved for Class II Division 1 rated areas. Their aluminum driver enclosures are rated type 4X making them ideal for arduous outdoor environments. All model offerings are fitted with a 316 stainless steel mounting bracket as standard.

General

Catalog Number	13310-411
Color	Gray (RAL7038)
Operating Temperature	-40 °F to +158 °F
Storage Temperature Range	-58 °F to +158 °F
Weather Rating	NEMA 4, 4X, 3R, 13

Electrical Ratings

Wattage	25 W
---------	------

Certifications And Compliance

Certification

- UL
- cUL

Certified Listed

UL 1480 Ed. 6

Hazardous Rating(s)

- Class II Division 1, FG, T6, Ta -40°C to +70°C
- Class II Division 2, FG, T6, Ta -40°C to +70°C
- Class III Division 1 & 2

Product Assets

[Literature - 25 Watt Speakers - UL Class II Division 1 \(Dust Environments\)](#)



A Hubbell brand