



Indoor / Outdoor Compression Driver - 13314 Series (8 ohm)

By Austdac
Catalog # 13314-001

A compression drivers that is designed to provide optimum performance in both commercial and industrial applications. These indoor/outdoor compression drivers are commonly used in light and heavy manufacturing facilities with high ambient noise, and corrosive and hazardous environments.

Features

- Low Distortion, Superior Sound
- Rain-Tight, Chemical Resistant Housing
- Suitable for Harsh or Corrosive Environments
- Variable Impedance Drivers
- Fits GAI-TRONICS' Horns with 1 3/8" - 18 UNEF Threads
- NEMA 4X

General

Catalog Number	13314-001
Operating Temperature	-40° C to +70° C (-40° F to +158° F)
UPC	850025795142

Dimensions



Weight	3.1 lb
--------	--------

Electrical Ratings

Impedance	8 ohm
-----------	-------

Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Div. 2, Groups A, B, C, D• Class II, Div. 2, Groups F, G• Class III, Div. 2
Nema Rating	4X

Product Assets

[Installation Manuals - Speaker/Horn Installation for GAI-TRONICS Communication Systems](#)
[Literature - Indoor / Outdoor Compression Driver](#)