



## UL Div 2, 25 Watt Speakers - 8 ohm

By Austdac  
Catalog # 13381-005

The 13381-005 to 13381-008 Series Loudspeakers are heavy duty, high output loudspeakers ideal for broadcasting speech announcements and electronic alarm tones in hazardous environments with high ambient noise levels.

### General

Catalog Number	13381-005
Material	UL94V0 PPS & ABS with 316 stainless steel bracket
Operating Temperature	-20 °C to + 55 °C
Weather Rating	NEMA Type 4, 4X, 13

### Dimensions

Diameter	8.6 in
Length	12.6 in
Weight	6 lb

### Electrical Ratings

Wattage	25 W
---------	------

### Certifications And Compliance

Certified Listed	<ul style="list-style-type: none"><li>UL File: E165792</li></ul>
------------------	--



### Hazardous Rating(s)

- UL File: 1480 & 1480A
- Class I, Div 2, ABCD T2C (230°C) at +55°C
- Class I, Div 2, ABCD T2D (215°C) at +40°C
- Class II, Div 2, FG T5 (100°C) at +55°C
- Class II, Div 2, FG T6 (85°C) at +40°C
- Class III, Div 1 & 2, T5 (100°C) at +55°C
- Class III, Div 1 & 2, T6 (85°C) at +40°C

### Product Assets

[Literature - UL Division 2, 25 Watt Speakers \[13381-005 to 13381-008 Series\]](#)  
[Specifications - 13381-005 Specification Sheet](#)