



# Corridor Telephone, Auto-dial ( Model 210-003)

By Austdac  
Catalog # 210-003



The corridor telephone offers standard line-powered telephone operation in a rugged, stainless steel package. Its volume-control handset includes a 29-inch, swivel armored cord and the microphone and earpiece are non-accessible. The 210-003 projects less than 4-inches from the mounting surface making it ADA-compliant for corridor installation.

## Application

Corridor Installations

## General

Catalog Number	210-003
Color	Silver
Connectivity Options	Analog
Mount location	Surface-Mount
Operating Temperature	-40° F to +140° F (-40° C to +60° C)
Output Level Ringer	90 dBA @ 2 ft.
Signal Type	Analog
Specifications	UL/IC/FCC
Type	Auto-dial
Weather Rating	Indoor

## Dimensions

Dimensions	3.27 in x 5.5 in x 10.0 in
Height	10 in
Length	3.27 in
Weight	5.5 lb
Width	5.5 in

## Electrical Ratings

Input Voltage	Phone Line
Signal	Phone Line

## Certifications And Compliance

Certified Listed	UL/IC/FCC
------------------	-----------

## Product Assets

- [Brochures - Rugged Telephone Brochure](#)
- [Installation Manuals - Analog Corridor Telephones - Model 210 Series](#)
- [Literature - Corridor Telephone](#)