



Auteldac 5 (analogue), black, curly cord, 0 button (CB): ATEX, noise cancelling with headset socket

By Austdac
Catalog # [212-02-5020-410](#)

The Auteldac 5 (A5) telephone is an ATEX and IECEx approved, weather resistant unit, designed to withstand arduous industrial atmospheres and environmental extremes.



Application

Hazardous Areas

General

CE Compliant	Yes
Catalog Number	212-02-5020-410
Color	Black
Connectivity Options	Analogue
Mount location	Surface-Mount
Operating Temperature	-20°C up to +60°C to -40°C up to +60 °C
Output Level Ringer	90 dBA @ 2 ft.
Signal Type	Analogue
Specifications	CE
Type	<ul style="list-style-type: none">• 0 Button• CB (Central Battery)
Weather Resistant	Yes

Dimensions

Dimensions	5.5 in x 7.5 in x 11.5 in
Height	11.5 in
Length	5.5 in
Weight	7 lb
Width	7.5 in

Electrical Ratings

Signal	Phone Line
--------	------------

Certifications And Compliance

CE Compliant	Yes
Certification	ATEX

Product Assets

[Installation Manuals - Guide d'installation et d'utilisation for Auteldac 5 Téléphone pour zone à risques certifiée zone 1 Ex](#)
[Installation Manuals - Auteldac 5 Zone 1 Ex Certified Hazardous Area Telephone Installation and User Guide](#)
[Literature - AUTEILDAC 5 - ATEX Approved Hazardous Area Telephone](#)