



Auteldac 5 (Analogue), curly cord, 18 button, ATEX, noise cancelling

By Austdac

Catalog # 212-02-5028-400

The Auteldac 5 (A5) telephone is an ATEX and IECEx approved, weather resistant unit, designed to withstand arduous industrial atmospheres and environmental extremes.



Application

Hazardous Areas

General

CE Compliant	Yes
Catalog Number	212-02-5028-400
Color	Black
Connectivity Options	Analogue
Mount location	Surface-Mount
Operating Temperature	-20°C up to +60°C to -40°C up to +60 °C
Output Level Ringer	90 dBA @ 2 ft.
Signal Type	Analogue
Specifications	CE
Type	18 Button
Weather Resistant	Yes

Dimensions

Dimensions 5.5 in x 7.5 in x 11.5 in

Height	11.5 in
Length	5.5 in
Weight	7 lb
Width	7.5 in

Electrical Ratings

Signal	Phone Line
--------	------------

Certifications And Compliance

CE Compliant	Yes
Certification	ATEX

Product Assets

[Installation Manuals - Guide d'installation et d'utilisation for Auteldac 5 Téléphone pour zone à risques certifiée zone 1 Ex](#)
[Installation Manuals - Auteldac 5 Zone 1 Ex Certified Hazardous Area Telephone Installation and User Guide](#)
[Literature - AUTEILDAC 5 - ATEX Approved Hazardous Area Telephone](#)