



# Tough Phone - Analog (Keypad)

By Austdac  
Catalog # 226-001

The Tough Phone series was developed for public and industrial areas requiring a virtually indestructible telephone. Housed in a 1/4-inch thick, sand-cast aluminum, weatherproof enclosure and coated with an exterior polyurethane finish.

## Features

- Cast Aluminum Enclosure with Polyurethane Finish
- Extended Temperature Range: - 40°F to +140°F
- Braille Metallic Keypad
- Hearing Aid Compatible
- Non-movable Hookswitch
- Volume Control Handset with Noise-canceling Microphone and 15-inch Armored Cord
- Non-volatile Electronic Memory (Stand-by Batteries Not Required)
- Conformal-coated PCBA
- NEMA 3R Weatherproof Rating
- FCC & IC Certified, UL60950 Listed

## Application

- Industrial Areas
- Public Areas

## General

Catalog Number	226-001
Color	Gray
Connectivity Options	Analog
Mount location	Surface-Mount
Output Level Ringer	74 dBA @ 2 ft.



Signal Type	Analog
Specifications	UL/CSA, FCC, IC
Type	Keypad
Weather Rating	NEMA 3R

## Dimensions

Dimensions	6.15 in x 9.7 in x 13.5 in
Height	13.5 in
Length	6.15 in
Weight	18 lb
Width	9.7 in

## Electrical Ratings

Input Voltage	Phone Line
Signal	Phone Line

## Certifications And Compliance

Certified Listed	UL/CSA, FCC, IC
------------------	-----------------

## Product Assets

- [Brochures - Rugged Telephone Brochure](#)
- [Installation Manuals - Rugged Analog Telephones with Keypads](#)
- [Literature - Rugged Telephones - Keypad](#)