



Hazardous Area Telephones - Tough Phone - Div. 2 (Analog)

By Austdac
Catalog # 226-002



The Analog Tough Phone, Model 226-002, provides fully-functional, line-powered communications that are approved for use in Class I, Division 2, Groups A, B, C, D; Class II, Division 2, Groups F and G; Class III classified areas. Our outdoor models have a Type 3R weatherproof rating. Housed in corrosion-resistant enclosures, these units offer superior resistance to chemicals, solvents, salts, and extreme temperatures. Each unit is equipped with a chrome-plated zinc keypad that is fully sealed to prevent entry of dirt, contaminants, and water. Model 226-002's armored cord is rated at 800 lbs. of pull strength. The non-movable handset cradle uses a proximity-detecting switch to take the phone off-hook.

Features

- Hazardous Area approved for: Class I, Division 2, Groups A, B, C, D
- Class II, Division 2, Groups F and G
- Class III
- Economical Communications for Division 2 Areas
- Indoor and Outdoor Models
- Anti-corrosive Enclosures
- Hearing Aid Compatible (HAC) with Pushbutton Volume Control
- Hytel Coiled Cord or Straight Armored Cord
- Sealed Chrome-plated Keypad
- Extreme Operating Temperature Range
- Conformal Coating on PCBA

General

| | |
|----------------------|----------------|
| Catalog Number | 226-002 |
| Color | Gray |
| Connectivity Options | Analog |
| Mount location | Surface-Mount |
| Output Level Ringer | 74 dBA @ 2 ft. |
| Signal Type | Analog |
| Specifications | UL/IC/FCC |
| Type | Keypad |
| Weather Rating | NEMA 3R |

Dimensions

| | |
|------------|---------------------------|
| Dimensions | 6.1 in x 9.7 in x 13.5 in |
| Height | 13.5 in |
| Length | 6.1 in |
| Weight | 18 lb |
| Width | 9.7 in |

Electrical Ratings

| | |
|---------------|------------|
| Input Voltage | Phone Line |
| Signal | Phone Line |

Certifications And Compliance

| | |
|---------------------|---|
| Certification | <ul style="list-style-type: none"> • UL • CSA • IC |
| Hazardous Rating(s) | <ul style="list-style-type: none"> • Class I, Division 2, Groups A, B, C, D • Class II, Division 2, Groups F & G • Class III, Division 2 |
| Nema Rating | NEMA 3R |

Product Assets

- [Brochures - Rugged Telephone Brochure](#)
- [Installation Manuals - Model 226-002, 341-001, and 351-001 Div. 2 Industrial Telephones](#)
- [Literature - Hazardous Area Telephones](#)
- [Specifications - 226-002](#)