



# Titan (SMART analogue), yellow, steel cord, 3 button - CE Marked

By Austdac  
Catalog # 226-02-0003-222

**Titan's** aluminium body is robust and designed to last longer in hostile outdoor environments. Along with weather and vandal resistance, the Titan range meets the acoustic performance, reliability and varying applications demanded by today's markets. **Self Monitoring and Reporting Telephones** can be integrated with GAI-TRONICS' **TMA monitoring and maintenance software**. **SMART** gives advanced features including remote programming, fault monitoring and call logging, all from a line-powered telephone capable of operating up to 7km from the exchange on a two-wire cable.

## General

CE Compliant	Yes
Catalog Number	226-02-0003-222
Color	Yellow
Connectivity Options	SMART Analogue
Mount location	Surface-Mount & Post-Mounting
Operating Temperature	-20° C to +60° C
Output Level Ringer	80 dBA @ 2 ft.
Signal Type	Analog
Specifications	CE
Storage Temperature Range	-40° C to +70° C
Type	3 Button
Weather Rating	IP66

## Dimensions

Dimensions	5.1 in x 8.07 in x 14.5 in
Dimensions - Shipping	15.5 x 8.75 x 5.5
Height	14.5 in



Length	5.1 in
Weight	11 lb
Width	8.07 in

## Electrical Ratings

Input Voltage	Phone Line
Signal	Phone Line

## Certifications And Compliance

CE Compliant	Yes
--------------	-----

## Product Assets

- [Certifications - Titan and Commander SMART Analogue Telephones Declaration of Conformity](#)
- [Installation Manuals - Installation and User Guide for Titan Telephone \(1088\) Commander Telephone \(1089\) SMART models](#)
- [Literature - Titan - Metal Bodied Weather Resistant Telephone \(Analogue, Smart Analogue, VoIP\)](#)
- [Specifications - 226020003222](#)



A Hubbell brand