



Tough Phone - VoIP (Auto-dial)

By Austdac
Catalog # 227-710

GAI-TRONICS' SIP compatible VoIP Handset Auto-dial Telephones are designed to provide direct point-to-point communication between personnel throughout a facility over an existing Internet Protocol LAN. The telephones are programmed to automatically dial when the handset is taken off-hook (number/address programming via imbedded web browser). The VoIP telephones are intended for connection to a 10/100 BaseT Ethernet SIP network and operate using power-over-Ethernet or an alternative power source.

Features

- Embedded Browser (No Additional Interface required) for Web Page Configuration
- Power Over Ethernet or Alternative 24 - 48 V dc Supply
- SIP Compatible
- RJ45 LAN or WAN Direct Connection
- Four Contact Inputs and Two Relay Outputs
- Real-time Email Fault Reporting
- Anti-corrosive Enclosures
- Surface Mount Models
- Auto-dial Operation
- Hearing Aid Compatible
- Non-moveable Hookswitch
- Noise-cancelling Microphone
- Noise-cancelling Microphone
- Volume Control Pushbutton
- Weather-resistant (Type 3R designs)
- Compatible with TMA (Telephone Management Application) Software

Application

- Outdoor Industrial Areas
- Public Areas (NEMA 3R)

General

Catalog Number	227-710
Color	Silver
Connectivity Options	VoIP
Mount location	Surface-Mount & Pole-Mount
Operating Temperature	-4°F to +131°F / -20°C to +55°C
Signal Type	VoIP - SIP



Specifications

Storage Temperature Range	UL/CSA, FCC -40° C to +70° C
Temperature Rating	-4°F to +131°F (-20°C to +55°C)
Type	Auto-Dial
Weather Rating	Type 3R

Dimensions

Cubic Capacity	805.3425 cu.in
Depth	6.15 in
Dimensions	6.1 in x 9.7 in x 13.5 in
Height	13.5 in
Length	6.1 in
Weight	14.5 lb
Width	9.7 in

Electrical Ratings

Signal	Ethernet
Voltage Rating Description	24-48 VDC or PoE

Certifications And Compliance

Certification	UL/CSA/FCC
Certified Listed	UL/CSA/FCC
Compliance	FCC CRF 47 Part 15

Product Assets

- [Brochures - Rugged Telephone Brochure](#)
- [Configuration Guide - VoIP Telephone Basic Configuration Guide](#)
- [Configuration Guide - VoIP Telephone Configuration Guide:](#)
- [Firmware versions 1193 Telephones \(v1.08\); 1201 Telephones for Auteldac 6 \(v1.08\)](#)
- [Installation Manuals - VoIP - Software Configuration](#)
- [Literature - VoIP Handset Rugged Telephone - Auto-dial](#)