



WiFi UL Class I Division 2 Telephone / PagePhone, NEMA 4X

By Austdac

Catalog # 351-8xxxxx

This NEMA 4X weather rated native VoIP device functions wirelessly when connected to an existing IP network. When properly equipped, this Telephone / PagePhone can provide a 30W output into a suitable 8 Ohm speaker for multicast broadcasts. Available in four (4) colors (gray, red, orange or yellow).

Features

- UL & cUL approval for: Class I, Division 2, Groups A,B,C,&D T6; Class II, Division 2, Groups F & G; Class III, Division 2
- NEMA 4X Weather Rating
- IEEE 802.11 b/g/n Compatibility
- AC Power or DC Power Connections
- Optional 30W Amplifier Output
- Optional Dual Relay Output (programmable)
- Optional Headset Connection
- 6-ft. Hytrel Coiled Cord
- Corrosion-resistant Construction

General

Catalog Number	351-8xxxxx
Color	Gray, red, orange, or yellow
Connectivity Options	WiFi



Enclosure Type Engineered Plastic, NEMA 4X

Dimensions

Weight 12.5 lb

Certifications And Compliance

Compliance	NEMA 4X (Enclosure)
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2, Groups A, B, C & D T6• Class II, Division 2, Groups F & G• Class III, Division 2

Product Assets

[Literature - VoIP UL Class I Division 2 Telephone / PagePhone](#)