



Analog UL Class I Div 1 Telephone

By Austdac Pty Ltd
Catalog # 352-001

GAI-Tronics introduces the world's first UL Class I Division 1 telephone and is available in standard analog. This rugged analog handset is UL approved to Class I Division 1 Groups B, C, & D, Class II Groups F & G and Class III, Type 4X, and ABS Type Approved. Analog variants are available with relay contact. Ring relay contacts are 5A, 250 V ac / 30 V dc rated.



General

Color	Gray
Connectivity Options	Analog
Mount location	Surface-Mount
Output Level Ringer	External required
Signal Type	Analog
Weather Rating	Type 4X

Dimensions

Cubic Capacity	1175.265 cu.in
Depth	9.36
Height	12.25 in
Weight	28 lb
Width	10.25 in

Electrical Ratings

Signal	Phone Line
--------	------------

Certifications and Compliance

Certification	<ul style="list-style-type: none">• UL• cUL
Compliance	Telecoms Compliance to Standards: FCC CFR 47 Part 15
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 1, Groups B, C, & D• Class II, Division 1, Groups F & G• Class III, Division 1

Product Assets

[Brochures - Rugged Telephone Brochure](#)
[Installation Manuals - Division 1 Telephones \(Model 352-001, 352-002, 352-003, and 352-004\)](#)
[Literature - UL Class I Division 1 Telephones \(VoIP / SMART / Analog\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
AUST-352-001-SPEC-EN | REV 7/2023