



VoIP Phone (Class I Div 1)

By Austdac Pty Ltd
Catalog # [352-701](#)

GAI-Tronics 352, introduces the world's first UL Class I Division 1 VoIP telephone. All models are UL approved to Class I Division 1 Groups B, C, & D, Class II Groups F & G and Class III, Type 4X, and ABS Type Approved. The native VoIP telephone, the 352 VoIP model does not need an IP convertor but connect directly to a SIP based VoIP telephone system.



Features

- Line Powered
- Noise Canceling Microphone
- Volume Adjust
- Type 4X Weather Rating

General

Color	Gray
Connectivity Options	VoIP
Mount location	Surface-Mount
Output Level Ringer	External required
Signal Type	VoIP - SIP
Type	VoIP
Weather Rating	Type 4X

Dimensions

Cubic Capacity	1175.265 cu.in
Depth	9.36
Dimensions	9.5 in x 10.25 in x 12.25 in
Height	12.25 in
Length	9.5 in
Weight	28 lb
Width	10.25 in

Electrical Ratings

Signal	Ethernet
Voltage Rating Description	24-48 VDC or PoE

Certifications and Compliance

Certification	<ul style="list-style-type: none">• UL• cUL
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 1, Groups B, C, & D• Class II, Division 1, Groups F & G• Class III, Division 1

Product Assets

[Brochures - Rugged Telephone Brochure](#)
[Installation Manuals - Division 1 VoIP Telephones \(Model 352-701 and 352-703\)](#)
[Literature - UL Class I Division 1 Telephones \(VoIP / SMART / Analog\)](#)



A proud member of the Hubbell Family.