



UL Division 1 VoIP Page Phone

By Austdac
Catalog # 352-712

This unique native VoIP phone comes equipped with an on-board 30W Class D amplifier. Utilized as an IP “telephone” and with a suitable eight ohm (8ff) loudspeaker connected to the device, the unit enables point to point calling with a “ring” tone generated to the loud-speaker (supplied separately). In multicast operation, the telephone is able to receive group pages. Each device may be a part of up to eight (8) paging groups.



Features

- Built in Class D Amplifier
- Noise-Canceling Microphone
- Volume Adjust

General

Catalog Number	352-712
Connectivity Options	VoIP
Mount location	Surface-Mount
Type	<ul style="list-style-type: none">• VoIP• Page Phone

Certifications And Compliance

Certification
Hazardous Rating(s)

- UL & cUL
- Class I, Division 1, Groups B, C, & D
 - Class II, Division 1, Groups F & G
 - Class III, Division 1, Part 15 compliant, T6 gas, T4a dust

Product Assets

- [Brochures - Rugged Telephone Brochure](#)
- [Installation Manuals - VoIP - Software Configuration](#)
- [Literature - World's First UL Division 1 VoIP Page Phone](#)