

NEMA 4X Rugged Telephone - Model 354-001 Series

By Austdac
Catalog # [354-001OR](#)



Model 354-001 Series NEMA 4X Telephones are designed for use in extreme weather conditions where temperature and moisture are a concern. They are ideal for use in areas that require a direct water spray (hose-down) for cleaning purposes or where a non-corrosive material is required. The 354-001 Series Telephone is perfectly suited for areas considered too harsh for a standard telephone.

Features

- Non-metallic, Corrosion-proof Enclosure NEMA 4X Weather Rating with Door Closed and Latched
- Line-powered, Analog Operation
- Heavy-duty Handset with Noise-cancelling Microphone, Hearing Aid Compatible Receiver, and Hytrel® Coiled Cord (6-ft. extended)
- Brushed Stainless Steel Front Panel with Push-button Volume Control
- Integral Ringer, 85 dB SPL
- Conformal-coated Printed Circuit Board
- Off-hook Detect Contact Closure Output
- -40° C to +60° C Temperature Range

General

Catalog Number	354-001OR
Color	Orange
Connectivity Options	Analog
Mount location	Surface-Mount
Output Level Ringer	85dBA @ 1 ft.
Signal Type	Analog
Specifications	UL/CSA, FCC, IC
Weather Rating	Type 4X

Dimensions

Dimensions	7.4 in x 9.4 in x 13.2 in
Height	13.2 in
Length	7.4 in
Weight	12 lb
Width	9.4 in

Electrical Ratings

Input Voltage	Phone Line
Signal	Phone Line

Certifications And Compliance

Certified Listed	UL/CSA, FCC, IC
Nema Rating	4X

Product Assets

- [Brochures - Rugged Telephone Brochure](#)
- [Installation Manuals - NEMA 4X Industrial Telephone \(Model 354-001 Series\)](#)
- [Literature - NEMA 4X Rugged Telephone \(Model 354-001 Series\)](#)
- [Specifications - 354-001OR](#)