



## NEMA 4X Rugged Telephone - Model 354-001 Series

By Austdac  
Catalog # [354-001ORSK](#)

Model 354-001 Series NEMA 4X Telephones are designed for use in extreme weather conditions where temperature and moisture are a concern. They are ideal for use in areas that require a direct water spray (hose-down) for cleaning purposes or where a non-corrosive material is required. The 354-001 Series Telephone is perfectly suited for areas considered too harsh for a standard telephone.

### General

|                      |                 |
|----------------------|-----------------|
| Catalog Number       | 354-001ORSK     |
| Color                | Orange          |
| Connectivity Options | Analog          |
| Mount location       | Surface-Mount   |
| Output Level Ringer  | 85dBA @ 1 ft.   |
| Signal Type          | Analog          |
| Specifications       | UL/CSA, FCC, IC |
| Type                 | Spring Door Kit |
| Weather Rating       | Type 4X         |

### Dimensions

|            |                           |
|------------|---------------------------|
| Dimensions | 7.4 in x 9.4 in x 13.2 in |
| Height     | 13.2 in                   |
| Length     | 7.4 in                    |
| Weight     | 12 lb                     |



|       |        |
|-------|--------|
| Width | 9.4 in |
|-------|--------|

### Electrical Ratings

|               |            |
|---------------|------------|
| Input Voltage | Phone Line |
| Signal        | Phone Line |

### Certifications And Compliance

|                  |                 |
|------------------|-----------------|
| Certified Listed | UL/CSA, FCC, IC |
| Nema Rating      | 4X              |

### Product Assets

- [Brochures - Rugged Telephone Brochure](#)
- [Installation Manuals - NEMA 4X Industrial Telephone \(Model 354-001 Series\)](#)
- [Literature - NEMA 4X Rugged Telephone \(Model 354-001 Series\)](#)