



NEMA 4X Rugged Telephone - Model 354-001 Series

By Austdac
Catalog # [354-001RDLD](#)

Model 354-001 Series NEMA 4X Telephones are designed for use in extreme weather conditions where temperature and moisture are a concern. They are ideal for use in areas that require a direct water spray (hose-down) for cleaning purposes or where a non-corrosive material is required. The 354-001 Series Telephone is perfectly suited for areas considered too harsh for a standard telephone.

General

| | |
|----------------------|-----------------|
| Catalog Number | 354-001RDLD |
| Color | Red |
| Connectivity Options | Analog |
| Mount location | Surface-Mount |
| Output Level Ringer | 85dBA @ 1 ft. |
| Signal Type | Analog |
| Specifications | UL/CSA, FCC, IC |
| Type | Keylock Door |
| Weather Rating | Type 4X |

Dimensions

| | |
|------------|---------------------------|
| Dimensions | 7.4 in x 9.4 in x 13.2 in |
| Height | 13.2 in |
| Length | 7.4 in |
| Weight | 12 lb |



| | |
|-------|--------|
| Width | 9.4 in |
|-------|--------|

Electrical Ratings

| | |
|---------------|------------|
| Input Voltage | Phone Line |
| Signal | Phone Line |

Certifications And Compliance

| | |
|------------------|-----------------|
| Certified Listed | UL/CSA, FCC, IC |
| Nema Rating | 4X |

Product Assets

- [Brochures - Rugged Telephone Brochure](#)
- [Installation Manuals - NEMA 4X Industrial Telephone \(Model 354-001 Series\)](#)
- [Literature - NEMA 4X Rugged Telephone \(Model 354-001 Series\)](#)