



NEMA 4X Rugged Telephone - Model 354-001 Series

By Austdac

Catalog # [354-001SK](#)



Model 354-001 Series NEMA 4X Telephones are designed for use in extreme weather conditions where temperature and moisture are a concern. They are ideal for use in areas that require a direct water spray (hose-down) for cleaning purposes or where a non-corrosive material is required. The 354-001 Series Telephone is perfectly suited for areas considered too harsh for a standard telephone.

General

Catalog Number	354-001SK
Color	Gray
Connectivity Options	Analog
Mount location	Surface-Mount
Output Level Ringer	85dBA @ 1 ft.
Signal Type	Analog
Specifications	UL/CSA, FCC, IC
Type	Spring Door Kit
Weather Rating	Type 4X

Dimensions

Dimensions	7.4 in x 9.4 in x 13.2 in
Height	13.2 in
Length	7.4 in
Weight	12 lb

Width 9.4 in

Electrical Ratings

Input Voltage	Phone Line
Signal	Phone Line

Certifications And Compliance

Certified Listed	UL/CSA, FCC, IC
Nema Rating	4X

Product Assets

[Brochures - Rugged Telephone Brochure](#)

[Installation Manuals - NEMA 4X Industrial Telephone \(Model 354-001 Series\)](#)

[Literature - NEMA 4X Rugged Telephone \(Model 354-001 Series\)](#)



A Hubbell brand