

NEMA 4X VoIP Rugged Handset Telephone - Model 354-711 Series (Auto-dial), Armored Cord, Gray

By Austdac
Catalog # [354-711AC](#)



GAI-TRONICS VoIP NEMA 4X Handset Auto-dial Telephones are designed to provide direct, point-to-point communications between personnel via an existing Internet Protocol LAN. These telephones are intended for connection to a 10/100 BaseT Ethernet SIP network and operate using Power-over-Ethernet (PoE) or an alternative, external power source. The 354-711 series VoIP Auto-dial Telephone offers true auto-dial functionality when the handset is removed from its cradle. This rugged telephone is weatherproof rated as NEMA 4X and will withstand a direct spray wash-down or severe weather conditions. The engineered plastic enclosure, conformal-coated printed circuit board, and stainless steel panel and hardware provide the maximum resistance to corrosion.

Features

- Non-metallic, Corrosion-proof Enclosure
- NEMA 4X Weather Rating
- SIP Compatible
- Power Over Ethernet or Alternative 24/48 V dc Supply
- Brushed Stainless Steel Front Panel with Push-button Volume Control
- Four Programmable Inputs and Two Contact Closure Outputs
- Conformal-coated Printed Circuit Board

Application

Outdoor & Indoor Use (NEMA 4X)

General

Catalog Number	354-711AC
Color	Gray
Connectivity Options	VoIP
Mount location	Surface-Mount
Operating Temperature	-4°F to +131°F / -20°C to +55°C
Signal Type	VoIP - SIP
Specifications	UL/CSA, FCC
Storage Temperature Range	-40° C to +70° C
Temperature Rating	-4°F to +131°F (-20°C to +55°C)
Type	<ul style="list-style-type: none"> • Cord Type: 15-in. Armored Cord • Auto-dial

Weather Rating

Type 4X

Dimensions

Cubic Capacity	1201.725 cu.in
Depth	10.5 in
Dimensions	14.6 in x 10.9 in x 10.5 in
Height	10.5 in
Length	14.6 in
Weight	15 lb
Width	10.9 in

Electrical Ratings

Signal	Ethernet
Voltage Rating Description	24-48 VDC or PoE

Certifications And Compliance

Certification	UL/CSA/FCC
Certified Listed	UL/CSA/FCC
Compliance	FCC CRF 47 Part 15
Nema Rating	4X

Product Assets

[Configuration Guide - VoIP Telephone Basic Configuration Guide Literature - NEMA 4X VoIP Handset Telephone, \(Auto-dial\), 354-711 Series](#)
[Specifications - 354-711AC](#)