



RED ALERT® Telephones - Model 392-001

By Austdac
Catalog # 392-001

GAI-TRONICS' Model 392-001 RED ALERT® Handsfree Telephone is designed to provide clear and reliable communications in almost any environment. The Model 392-001 is considered to be Type 3R weatherproof compliant when installed in a GAI-Tronics surface-mount enclosure, free-standing stanchion, wall-mount stanchion or simply recessed into an existing wall.

Features

- Weather-resistant (Type 3R) Flush-Mount Design
- Telephone Line Powered, (No Battery or External Power Required for Telephone Operation)
- CALL Pushbutton for Keypad Use
- Standard or SMART Operation
- Braille, Sealed Chrome-plated Keypad
- Auto Answer (with Silent Monitoring)
- (2) Programmable Auxiliary Outputs for Peripheral Equipment Control
- Operating Range of -20° C to +60° C
- Call Received When Lit LED
- 14-gauge Brushed Stainless Steel Panel
- 16-gauge Cold-Rolled Steel Back Box with Black Polyurethane Finish
- Silkscreened Graphics
- UL/CSA 60950 Compliant
- FCC Part 68 Certified
- ADA Compliant

General

Catalog Number	392-001
Color	Silver
Connectivity Options	Analog
Mount location	Flush-Mount
Output Level Speaker	87 dB @ 1 M



Signal Type	Analog
Specifications	UL/CSA, FCC, IC
Type	Access Telephones
Weather Rating	Type 4X

Dimensions

Dimensions	4.0 in x 8.0 in x 9.5 in
Height	9.5 in
Length	4 in
Weight	7.2 lb
Width	8 in

Electrical Ratings

Input Voltage	Phone Line
Signal	Phone Line

Certifications And Compliance

Certified Listed	UL/CSA, FCC, IC
------------------	-----------------

Product Assets

- [Brochures - Red Alert Telephone Brochure](#)
- [Installation Manuals - RED ALERT® 300 Series Emergency Telephone Manual](#)
- [Literature - Telephone Management Application \(TMA\)](#)
- [Literature - RED ALERT Hands-free Telephones](#)