



# Low Voltage LED Strobe, 12-24 V dc

By Austdac  
Catalog # 541-001

The Low Voltage LED Strobe offers constant on/off modes with flashing operation in a low-voltage, 12-24 V dc package. The 541-001 also includes a secondary contact closure output for auxiliary equipment control. In the constant-on mode, the glow of the LED tower remains steady for location purposes and, when activated, will flash at a rate of 240 flashes per minute.

## Features

- High Visibility, Even in Daylight
- UL Listed for Outdoor Wet Locations
- Low Operating Temperature
- 240 Flashes Per Minute
- UL/cUL Listed
- Dry Contact Closure Output

## General

Catalog Number	541-001
Weather Rating	UL "Outdoor Wet" Locations

## Dimensions

Height	7 in
--------	------



Width	6.5 in
-------	--------

## Certifications And Compliance

Certified Listed	UL 1638A / CSA C22.2 No. 205-12
------------------	---------------------------------

## Product Assets

- [Installation Manuals - Model 541-001 LED Strobe with Constant-On/Off Modes](#)
- [Installation Manuals - Model 4115A Surface-Mount Strobe Mounting Bracket Assembly](#)
- [Literature - Low Voltage LED Strobe \(Model 541-001\)](#)
- [Sales Drawings - Strobe Mounting Details - 4115A](#)
- [Specifications - 541001](#)



A Hubbell brand