

## Plant Paging Station

By Austdac  
Catalog # 670-002

Hazardous Area Speaker Amplifier Station for 24 VDC operation,  
FM- and CSA-approved for selected Division 1 areas.



### Features

- Page Party Speaker Amplifier
- DIV2

### General

Catalog Number	670-002
Color	Gray
Material	Aluminum
Output Level Speaker	8 / 16 Ohm
Power	12 W
Series	Page/Party®
Signal Type	Analog
Weather Rating	Indoor

### Dimensions

Cubic Capacity	579.544 cu.in
Depth	5.6
Height	13.1 in

Weight	27 lb
Width	7.9 in

### Electrical Ratings

Input Voltage	24 VDC
Signal	33 Ohm

### Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 1

### Product Assets

[Brochures - Page/Party® Solutions Brochure](#)  
[Brochures - Page/Party® Accessories Guide](#)  
[Installation Manuals - 700 Series 24 VDC Page/Party® System Design and Installation](#)  
[Installation Manuals - 24 VDC Explosion-proof Speaker Station - Model 670-002](#)  
[Specifications - 670-002](#)