



Plant Paging/Intercom Amplifier

By Austdac
Catalog # 701-302

Handset/Speaker Amplifier with handset pressbar and magnetic hookswitch



General

Catalog Number	701-302
Color	Gray
Material	Steel
Output Level Speaker	8 / 16 Ohm
Power	12 W
Series	Page/Party®
Signal Type	Analog
UPC	850025795012
Weather Rating	Indoor

Dimensions

Cubic Capacity	426.465 cu.in
Depth	6.5
Height	8.1 in
Weight	6.8 lb

Width 8.1 in

Electrical Ratings

Input Voltage	120 VAC
Signal	33 Ohm

Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

Product Assets

[Brochures - Page/Party® Solutions Brochure](#)
[Brochures - Page/Party® Accessories Guide](#)
[Installation Manuals - 701-302 Handset/Speaker Amplifier](#)
[Kit Manuals - PVC Coil Cord Replacement Kit](#)