



# Plant Paging/Intercom Amplifier

By Austdac  
Catalog # 701-307

Handset/Speaker Amplifier, 24 VDC with Magnetic Hookswitch,  
FM Approved



## General

Catalog Number	701-307
Color	Gray
Material	Steel
Output Level Speaker	8 / 16 Ohm
Power	12 W
Series	Page/Party®
Signal Type	Analog
Weather Rating	Indoor

## Dimensions

Cubic Capacity	426.465 cu.in
Depth	6.5
Height	8.1 in
Weight	6.8 lb
Width	8.1 in

## Electrical Ratings

Input Voltage	24 VDC
Signal	33 Ohm

## Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

## Product Assets

- [Brochures - Page/Party® Solutions Brochure](#)
- [Brochures - Page/Party® Accessories Guide](#)
- [Installation Manuals - Handset/Speaker Amplifier \(24 V DC\) - Model 701-307](#)
- [Kit Manuals - PVC Coil Cord Replacement Kit](#)