

## Plant Paging/Intercom Amplifier

By Austdac  
Catalog # 701-309

24 V dc Handset/Speaker Amplifier - 12 Watt Speaker Amplifier -  
Listed for Division 2 Areas - Auxiliary Jack



### Features

- Page Party Handset/Speaker Amplifier
- Magnetic Hookswitch

### General

|                      |             |
|----------------------|-------------|
| Catalog Number       | 701-309     |
| Color                | Gray        |
| Material             | Steel       |
| Output Level Speaker | 8 / 16 Ohm  |
| Power                | 12 W        |
| Series               | Page/Party® |
| Signal Type          | Analog      |
| Weather Rating       | Indoor      |

### Dimensions

|                |               |
|----------------|---------------|
| Cubic Capacity | 426.465 cu.in |
| Depth          | 6.5           |
| Height         | 8.1 in        |

|        |        |
|--------|--------|
| Weight | 6.8 lb |
| Width  | 8.1 in |

### Electrical Ratings

|               |        |
|---------------|--------|
| Input Voltage | 24 VDC |
| Signal        | 33 Ohm |

### Certifications And Compliance

|                     |          |
|---------------------|----------|
| Certified Listed    | UL       |
| Hazardous Rating(s) | UL Div 2 |

### Product Assets

[Brochures - Page/Party® Solutions Brochure](#)  
[Brochures - Page/Party® Accessories Guide](#)  
[Installation Manuals - 42003-243A Kit Manual](#)  
[Installation Manuals - 24 V DC Handset/Speaker Amplifier with Auxiliary Jack - Model 701-309](#)  
[Specifications - 701-309](#)