

Plant Paging Amplifier

By Austdac

Catalog # 751-002VC

Speaker Amplifier, 24 VDC with remote volume control.



Features

- Page Party Intercom System
- Volume Level Control

General

Catalog Number	751-002VC
Color	Gray
Material	Steel
Output Level Speaker	8 / 16 Ohm
Power	12 W
Series	Page/Party®
Signal Type	Analog
Weather Rating	Indoor

Dimensions

Cubic Capacity	196.83 cu.in
Depth	3

Height	8.1 in
Weight	5 lb
Width	8.1 in

Electrical Ratings

Input Voltage	24 VDC
Signal	33 Ohm

Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

Product Assets

[Brochures - Page/Party® Solutions Brochure](#)
[Brochures - Page/Party® Accessories Guide](#)
[Installation Manuals - Volume Level Control Receiver Assembly](#)
[Instruction Sheet](#)
[Specifications - 751-002VC](#)