

## Plant Paging Station

By Austdac  
Catalog # 810-330D200

ICS Indoor Speaker Amplifier Station - 100-240VAC - UL Class I, Div. 2 - 8-ohm speaker output with VLC - RTU relay output - Gray finish



### Features

Industrial Communication System

### General

Catalog Number	810-330D200
Color	Gray
Material	Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Type	<ul style="list-style-type: none"><li>• Speaker Amplifier Station</li><li>• Indoor Speaker Amplifier Stations</li></ul>
Weather Rating	NEMA Type 12

### Dimensions

Cubic Capacity	610.90965 cu.in
----------------	-----------------

Depth	5.07 in
Height	14.5 in
Weight	11 lb
Width	8.31 in

### Electrical Ratings

Input Voltage	100-240 VAC
Signal	33 Ohm
Voltage Rating	100-240 VAC

### Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

### Product Assets

[Installation Manuals - ICS Class I, Div. 2 Page/Party® Station Literature - ICS Amplifiers](#)  
[Specifications - 810-330D200](#)