




## Plant Paging Station

By Austdac

Catalog # 810-340D1R0

ICS SmartSeries Indoor Speaker Amplifier Station - 100-240VAC  
- UL Class I, Div. 2 - 70/100V speaker output - SmartSeries  
features - Orange finish



### General

Catalog Number	810-340D1R0
Color	Orange
Material	Steel
Output Level Speaker	70/100 V
Power	24 W
Series	ICS
Signal Type	Analog
Type	<ul style="list-style-type: none"><li>• Speaker Amplifier Station</li><li>• Indoor Speaker Amplifier Stations</li></ul>
Weather Rating	NEMA Type 12

### Dimensions

Cubic Capacity	610.90965 cu.in
Depth	5.07 in

Height	14.5 in
Weight	11 lb
Width	8.31 in

### Electrical Ratings

Input Voltage	100-240 VAC
Signal	33 Ohm
Voltage Rating	100-240 VAC

### Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

### Product Assets

[Installation Manuals - ICS Class I, Div. 2 Page/Party® Station Literature - ICS Amplifiers](#)