



# Plant Paging Station

By Austdac  
Catalog # [810-710D2S0](#)

ICS Indoor Speaker Amplifier Station - 24VDC - UL Class I, Div. 2  
- 70/100V speaker output - Gray finish, PCBA tropicalization



## General

|                      |   |
|----------------------|---|
| Catalog Number       | 810-710D2S0   |
| Color                | Gray  |
| Material             | Steel   |
| Output Level Speaker | 8 Ohm   |
| Power                | 30 W  |
| Series               | ICS   |
| Signal Type          | Analog  |
| Type                 | <ul style="list-style-type: none"><li>• Speaker Amplifier Station</li><li>• Indoor Speaker Amplifier Stations</li></ul> |
| Weather Rating       | NEMA Type 12  |

## Dimensions

|                |                 |
|----------------|-----------------|
| Cubic Capacity | 610.90965 cu.in |
| Depth          | 5.07 in         |

|        |         |
|--------|---------|
| Height | 14.5 in |
| Weight | 11 lb   |
| Width  | 8.31 in |

## Electrical Ratings

|                |        |
|----------------|--------|
| Input Voltage  | 24 VDC |
| Signal         | 33 Ohm |
| Voltage Rating | 24 VDC |

## Certifications And Compliance

|                     |          |
|---------------------|----------|
| Certified Listed    | UL       |
| Hazardous Rating(s) | UL Div 2 |

## Product Assets

[Installation Manuals - ICS Class I, Div. 2 Page/Party® Station Literature - ICS Amplifiers](#)