



Plant Paging/Intercom Station

By Austdac

Catalog # 811-211B100

ICS Indoor Handset/Speaker Single-party Station, 100-240 VAC, CE Safe area, 8-ohm speaker output, Headset jack, Orange finish, 6' PVC handset cord



General

Catalog Number	811-211B100
Color	Orange
Material	Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Type	<ul style="list-style-type: none">• Single Party• Headset Jack• 8-ohm speaker output
Weather Rating	NEMA Type 12

Dimensions

Cubic Capacity	985.6491 cu.in
Depth	8.18 in
Height	14.5 in

Weight	12 lb
Width	8.31 in

Electrical Ratings

Input Voltage	100-240 VAC
Signal	33 Ohm
Voltage Rating	100-240 VAC

Certifications And Compliance

Certified Listed	CE
Hazardous Rating(s)	CE Safe Area

Product Assets

[Installation Manuals - ICS Page/Party® Handset/Speaker Amplifier Station](#)
[Literature - ICS Indoor Stations](#)