



Plant Paging/Intercom Station

By Austdac
Catalog # 815-151D1R0

ICS SmartSeries Indoor Handset/Speaker Multi-party Station, 100-240 VAC, UL Class I, Div. 2, 70/100V speaker output, SmartSeries features with RTU input/output, Orange finish, 6' PVC handset cord



General

Catalog Number	815-151D1R0
Color	Orange
Material	Steel
Output Level Speaker	70/100 V
Power	24 W
Series	ICS SmartSeries
Signal Type	Analog
Type	<ul style="list-style-type: none">Multi-PartySmartSeries with RTU70/100V speaker output
Weather Rating	NEMA Type 12

Dimensions

Cubic Capacity	985.6491 cu.in
Depth	8.18 in

Height	14.5 in
Weight	12 lb
Width	8.31 in

Electrical Ratings

Input Voltage	100-240 VAC
Signal	33 Ohm
Voltage Rating	100-240 VAC

Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

Product Assets

[Installation Manuals - ICS Class I, Div. 2 Page/Party® Station Literature - ICS Indoor Stations](#)