

## Plant Paging/Intercom Station

By Austdac  
 Catalog # 815-254D100

ICS SmartSeries Indoor Handset/Speaker Multi-party Station, 100-240 VAC, UL Class I, Div. 2, 8-ohm speaker output with SmartVolume, SmartSeries features with RTU input/output, Headset jack - Orange finish, 25' Hytrel handset cord



### Features

Industrial Communication System

### General

Catalog Number	815-254D100
Color	Gray
Material	Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS SmartSeries
Signal Type	Analog
Type	<ul style="list-style-type: none"> <li>• Multi-Party</li> <li>• 8-ohm speaker output with SmartVolume</li> </ul>
Weather Rating	NEMA Type 12

### Dimensions

Cubic Capacity	985.6491 cu.in
----------------	----------------

Depth	8.18 in
Height	14.5 in
Weight	12 lb
Width	8.31 in

### Electrical Ratings

Input Voltage	100-240 VAC
Signal	33 Ohm
Voltage Rating	100-240 VAC

### Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

### Product Assets

- [Installation Manuals - ICS Class I, Div. 2 Page/Party® Station](#)
- [Literature - ICS Indoor Stations](#)
- [Specifications - 815-254D100](#)