



Plant Paging/Intercom Station

By Austdac

Catalog # 815-541D100

ICS SmartSeries Indoor Handset/Speaker Multi-party Station, 24 VDC, UL Class I, Div. 2, 8-ohm speaker output with SmartVolume, SmartSeries features, Orange finish, 6' PVC handset cord



General

| | |
|----------------------|---|
| Catalog Number | 815-541D100 |
| Color | Orange |
| Material | Steel |
| Output Level Speaker | 8 Ohm |
| Power | 30 W |
| Series | ICS SmartSeries |
| Signal Type | Analog |
| Type | <ul style="list-style-type: none">Multi-Party8-ohm speaker output with SmartVolume |
| Weather Rating | NEMA Type 12 |

Dimensions

| | |
|----------------|----------------|
| Cubic Capacity | 985.6491 cu.in |
| Depth | 8.18 in |

| | |
|--------|---------|
| Height | 14.5 in |
| Weight | 12 lb |
| Width | 8.31 in |

Electrical Ratings

| | |
|----------------|--------|
| Input Voltage | 24 VDC |
| Signal | 33 Ohm |
| Voltage Rating | 24 VDC |

Certifications And Compliance

| | |
|---------------------|----------|
| Certified Listed | UL |
| Hazardous Rating(s) | UL Div 2 |

Product Assets

[Installation Manuals - ICS Class I, Div. 2 Page/Party® Station](#)
[Literature - ICS Indoor Stations](#)