



Plant Paging Station

By Austdac
Catalog # 820-310D100

ICS Outdoor Speaker Amplifier Station - 100-240VAC - UL Class I, Div. 2 - 8-ohm speaker output - Orange finish



General

| | |
|----------------------|--|
| Catalog Number | 820-310D100 |
| Color | Orange |
| Material | GRP / Steel |
| Output Level Speaker | 8 Ohm |
| Power | 30 W |
| Series | ICS |
| Signal Type | Analog |
| Type | <ul style="list-style-type: none">• Speaker Amplifier Station• Outdoor Speaker Amplifier Stations |
| Weather Rating | NEMA Type 4X |

Dimensions

| | |
|----------------|---------------|
| Cubic Capacity | 1670.97 cu.in |
| Depth | 10.5 in |
| Height | 14.6 in |

| | |
|--------|---------|
| Weight | 13 lb |
| Width | 10.9 in |

Electrical Ratings

| | |
|----------------|-------------|
| Input Voltage | 100-240 VAC |
| Signal | 33 Ohm |
| Voltage Rating | 100-240 VAC |

Certifications And Compliance

| | |
|---------------------|----------|
| Certified Listed | UL |
| Hazardous Rating(s) | UL Div 2 |

Product Assets

[Installation Manuals - ICS Class I, Div. 2 Weatherproof Page/Party® Station](#)
[Literature - ICS Amplifiers](#)