

## Plant Paging Station

By Austdac  
 Catalog # 820-320D100

ICS Outdoor Speaker Amplifier Station - 100-240VAC - UL Class I, Div. 2 - 8-ohm speaker output with VLC - Orange finish



### Features

Industrial Communication System

### General

Catalog Number	820-320D100
Color	Orange
Material	GRP / Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Type	<ul style="list-style-type: none"> <li>• Speaker Amplifier Station</li> <li>• Outdoor Speaker Amplifier Stations</li> </ul>
Weather Rating	NEMA Type 4X

### Dimensions

Cubic Capacity	1670.97 cu.in
----------------	---------------

Depth	10.5 in
Height	14.6 in
Weight	13 lb
Width	10.9 in

### Electrical Ratings

Input Voltage	100-240 VAC
Signal	33 Ohm
Voltage Rating	100-240 VAC

### Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

### Product Assets

- [Installation Manuals - ICS Class I, Div. 2 Weatherproof Page/Party® Station](#)
- [Literature - ICS Amplifiers](#)
- [Specifications - 820-320D100](#)